


FBX545B



FBX545A



Model: FBX545

Wall mount IP65 wireless call button (with 1 meter wire)

Features:

- FBX545A/B: 1 button for calling and 1 for cancellation
- Wired button for CALL (much like a bed button)
- X mark button to CANCEL
- 1 Blue light indicator glows on call button press
- Buzzing sound on press of any of the CALL buttons
- Difference between **FBX545A and FBX545B models is the type and number of call button**

Technical details:

- Transmitter PA +10dbm
- Operating frequency: 380 – 480 MHz
- System operates works on signal hop mechanism. Signal transmission happens at more than 12-15 predefined frequencies
- Modulation type: GFSK
- Radio IC: CC1100 (Chipcon/TI) sub-GHz frequency
- Data packet error correction mechanism: FEC

Battery and operating voltage:

- 12 Volt (DC battery)
- Battery model: 23A
- Battery life: 2-3 years
- Battery type: Alkaline (dry)
- Battery replaceable: Yes
- Battery rechargeable: No
- Battery mounting: Bottom
- Battery life: 3-4years, depending on the usage

RF antenna:

PCB trace antenna / wire coil antenna / metal antenna (depends on environment necessity)

Mounting provisions:

Wireless wall mount calling button needs to be secured on the wall or any vertical surface using 4 screws

Application and features:

- Nurse call system for hospitals: remote with patients
- Steam bath sauna rooms / spas / restaurants etc.
- OPD token system for dispensaries: remote with doctors
- Office peon calling system: remote with clerk / manager
- Guest house attendant call unit: remote with customers in room

Precautions and mounting locations:

- Mounted on the top of door / wall / bed
- Easy mounting with 4 screws to secure it tightly
- IP65 enclosure unit, robust and weatherproof
- Keep away from metallic enclosures
- Do not expose battery to water and moisture

Wall mount calling unit:

Enclosure type: IP 65 (color grey)
Size: 150 x 90 x 55 mm
Weight: 230 gms

Range of communication:

- 20-30 meters indoors (depending on environmental condition)
- 100-150 meters outdoors (in open line of sight)

Pressing the button for at least 2-3 seconds improves the range of communication

FORBIX SEMICON INDIA PVT. LTD.

Bangalore, India

Website: <https://www.forbixindia.com>

+91 9742370190 / +91 9742159846

FORBIX Osäuhing,

Tallinn, Estonia

Website: <https://www.forbix.eu>

+372 880 1510

Email: sales@forbixindia.com