

# FBXWACS09C: 9 remote wireless calling system

## Technical specification



**Model: FBXWACS09C**

### 9 remote + 3 cancellation wireless calling system

#### Features:

- 9 BLUE indicator – one for each corresponding remote
- 3 additional remotes for cancellation
- 1 green light indicator for power supply (on indicator receiver)
- 1 buzzer, blows when call button pressed
- Adjust buzzer volume by volume controller
- Remote has 1 red light indicator to indicate button press
- Remote TOP button: to call (summon) peon
- Remote BOTTOM button: to cancel the call
- Red button to RESET system

#### Technical details:

- Remote transmitter PA +10dbm
- Receiver sensitivity: – 110dbm
- Operating frequency: 380 – 480 MHz
- System operates works on signal hop mechanism. Signal transmission happens at more than 12-15 predefined frequencies
- Modulation type: GFSK
- Radio IC: CC1100 (Chipcon/TI) and other equivalents in sub-GHz freq.
- Modulation: GFSK
- Data packet error correction mechanism: FEC

#### Operating voltage:

##### Remote controller

- 12 Volt DC battery (at the bottom)
- Battery model: 23A
- Battery life: 2-3 years
- Battery type: Alkaline (dry)
- Battery replaceable: Yes
- Battery rechargeable: No

##### Receiver indicator

- 12 Volt DC (110-220VAC/50-60Hz) adapter supplied

#### Signal transmissions:

Make sure to press a button for at least 2-3 seconds for reliable transmission. This increases the range of communication

#### Application and features:

- Nurse call system for hospitals: remote with patients
- Steam bath sauna rooms / spas / restaurants etc.
- OPD token system for dispensaries: remote with doctors
- Office peon calling system: remote with clerk / manager
- Office peon calling, school peon calling system

#### Range of communication:

- 20 – 30 meters indoors
- 100 – 120 meters outdoors (line of sight)

#### Precautions and mounting locations:

- Remotes mounted on the top of door / wall / bed
- Easy mounting of remote jacket with 2 screws
- For indoor purpose use only
- Keep away from metallic enclosures
- Do not connect the battery in opposite direction

- Receiver unit can mount on the wall
- Or even simply kept on the table

#### Wireless peon calling system:

Receiver indicator Size: 180 x 180 x 35 mm

Weight: 380 gms

Remote controller size: 120 x 40 x 20 mm

Remote controller weight: 45 gms

**FORBIX SEMICON INDIA PVT. LTD.**

Bangalore, India

Website: <https://www.forbixindia.com>

+91 9742370190 / +91 9742159846

**FORBIX Osäuhing,**

Tallinn, Estonia

Website: <https://www.forbix.eu>

+372 880 1510

Email: [sales@forbixindia.com](mailto:sales@forbixindia.com)